YOUR IMAGINATION... OUR INNOVATION...



Sigma WIP

- > SYSTEM HAVING 3 NOS. WATER INLET LINE (PORTABLE, HOT, PURIFIED WATER)
- > 2Nos. of output line for washing bigger Equipments
- USED HIGH PRESSURE CENTRIFUGAL PUMP WITH DISPLACEMENT OF 1200 LHP
- > 10 LITER DETERGENT TANK IS AN INBUILT FEATURE



- CONTROLLED THROUGH PLC WITH 99 RECIPE MANAGEMENT AND PRINTING FACILITY
- CLEANING SOP CAN BE DEFINE ON TIME BASE OR INDIVIDUAL WATER FLOW MANAGEMENT
- > VFD CAN BE PROVIDED ON REQUEST
- 21 CFR PART 11 COMPLY MODEL

THE FUNDAMENTAL NORMS OF GMP "MAINTAIN THE PURITY OF PHARMACEUTICAL MACHINERY" WITH SIGMA WIP/CIP SYSTEM



